

Model KB 23 | Cooling incubators with compressor technology

The most versatile among the cooled incubators for microorganisms: The BINDER KB series cooled incubator controls temperature ranges of -5 °C to 100 °C. With its comprehensive program functions, this cooled incubator offers a wide range of capabilities and delivers reproducible test results.

BENEFITS

- · Safe, reproducible incubation, even at high ambient temperatures
- Disinfection routine at 100 °C
- Up to 30% lower energy consumption compared to the previous model



Model 23

MAIN FEATURES

- Temperature range: 0 °C to 100 °C
- APT.line[™] preheating chamber technology
- Cooling with compressor cooling unit
- · Adjustable fan speed
- · Controller with time-segment and real-time programming
- Elapsed time indicator



- · Inner door made of tempered safety glass
- 2 stainless steel racks
- Stackable
- Class 3.1 independent temperature safety device (DIN 12880) with visual and audible temperature alarm
- Computer interface: RS 422

ORDERING INFORMATION

| Interior volume [cu.ft.] | Voltage | Option model | Version | ArtNo. |
|--------------------------|---------------------|--------------|--------------|-----------|
| Model KB 23 | | | | |
| 0.7 | 230 V 1 ph 50/60 Hz | Standard | KB023-230V | 9020-0112 |
| | 120 V 1 ph 60 Hz | Standard | KB023UL-120V | 9020-0113 |

TECHNICAL DATA

| Description | KB023-230V ¹ | KB023UL-120V ¹ | |
|---|-------------------------|---------------------------|--|
| Article Number | 9020-0112 | 9020-0113 | |
| Performance Data Temperature | | | |
| Temperature range [°C] | 0100 | 0100 | |
| Temperature variation at 37 °C [± K] | 0.3 | 0.3 | |
| Temperature fluctuation at 37 °C [± K] | 0.1 | 0.1 | |
| Heating-up time to 37 °C [min] | 11 | 11 | |
| Recovery time after 30 seconds door open at 37 °C [min] | 2 | 2 | |
| | | | |


1 All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10 %. The temperature data is determined in accordance to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. Technical data refers to 100 % fan speed. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.



| Description | KB023-230V ¹ | KB023UL-120V ¹ |
|-------------------------------------|-------------------------|---------------------------|
| Article Number | 9020-0112 | 9020-0113 |
| Electrical data | | |
| Rated Voltage [V] | 230 | 120 |
| Power frequency [Hz] | 50/60 | 60 |
| Nominal power [kW] | 0.3 | 0.3 |
| Unit fuse [A] | 10 | 12.5 |
| Phase (Nominal voltage) [ph] | 1 | 1 |
| Outer dimensions | | |
| Width net [mm] | 435 | 435 |
| Height net [mm] | 620 | 620 |
| Depth net [mm] | 520 | 520 |
| Wall clearance back [mm] | 100 | 100 |
| Wall clearance sidewise [mm] | 100 | 100 |
| Doors | | |
| Inner doors | 1 | 1 |
| Unit doors | 1 | 1 |
| Internal Dimensions | | |
| Width [mm] | 222 | 222 |
| Height [mm] | 330 | 330 |
| Depth [mm] | 277 | 277 |
| Measures | | |
| Interior volume [L] | 20 | 20 |
| Net weight of the unit (empty) [kg] | 44 | 44 |
| permitted load [kg] | 25 | 25 |
| Load per rack [kg] | 10 | 10 |
| Environment-specific data | | |
| Energy consumption at 40 °C [Wh/h] | 60 | 60 |
| Sound-pressure level [dB(A)] | 47 | 47 |
| Fixtures | | |
| Number of shelves (std./max.) | 2/3 | 2/3 |

1 All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10 %. The temperature data is determined in accordance to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. Technical data refers to 100 % fan speed. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.

DIMENSIONS incl. fittings and connections [mm]







| Designation | Description | * | ArtNo. |
|------------------------------------|--|--------|-----------|
| | back | | |
| | 10 mm | 01 | 8012-0395 |
| | 30 mm | 01 | 8012-1292 |
| | 50 mm | 01 | 8012-1294 |
| | left | | |
| | 10 mm | 01 | 8012-0393 |
| | 30 mm | 01 | 8012-1157 |
| ccess port with silicone | right | | |
| pidg | 10 mm | 01 | 8012-0392 |
| | 30 mm | 01 | 8012-1154 |
| | top | | |
| | 10 mm | 01 | 8012-0391 |
| | 30 mm | 01 | 8012-1151 |
| | 50 mm | 01 | 8012-1160 |
| | 100 mm | 01, 10 | 8012-1167 |
| nalog output 4-20 mA | for temperature values (output not adjustable) | 02 | 8012-0434 |
| Calibration certificate, xpanded | for temperature; for extending the measurement in center of chamber to include another test temperature | - | 8012-1120 |
| | for temperature, measurement in center of chamber at specified temperature | - | 8012-1139 |
| alibration certificate, | temperature measurement incl. certificate and 27 measuring points at specified temperature | - | 8012-1598 |
| emperature | temperature measurement incl. certificate, 15-18 measuring points at specified temperature | - | 8012-1577 |
| | temperature measurement incl. certificate, 9 measuring points at specified temperature | - | 8012-1556 |
| ata Logger Kit | T 220: For continuous temperature logging from -90 °C to 220 °C. The kit includes 1 data logger, Pt 100 sensor with 2 m extension cable and 1 magnetic fixture for mounting to the BINDER unit | 19 | 8012-0715 |
| oata Logger Software | LOG ANALYZE software kit, configuration and evaluation software for all BINDER Data Logger Kits (incl. USB data cable) | 19 | 8012-0821 |
| oor lock | lockable door handle | - | 8012-1250 |
| | RS 422 cable set and RS 232 / RS 422 interface converter for connection to 10-way plug distributor or for connection to a unit | | |
| | 120 V, 60 Hz option model | - | 8012-0557 |
| 4 | 230 V, 50/60 Hz option model | - | 8012-0556 |
| iterface converter | RS 422 cable set and RS 422 / Ethernet interface converter for connection to 10-way plug distributor or for connection to a unit | | |
| | 120 V, 60 Hz option model | - | 8012-0405 |
| | 230 V, 50/60 Hz option model | - | 8012-0380 |
| nterface converter, ISB / RS422 | RS 422 cable set and RS 422 / USB interface converter for connection to 10-way plug distributor or for connection to a unit (USB-powered converter) | - | 8012-0665 |
| nterior socket | Waterproof, switched flush-mounting box (CA3GD) for nominal voltage in unit interior, with cover and corresponding plug (nominal voltage; max. 500 W; max. 90 °C; protection class IP67) | 07 | 8012-1171 |
| H-neutral detergent | concentrated, for gentle remove of residual contaminants; 1 kg | - | 1002-0016 |
| t 100 temperature ensor | additional flexible Pt 100, interior, with external connection incl. LEMO connector (3-pin) | - | 8012-1177 |
| ack | stainless steel | - | 6004-0051 |
| ack accessories | Rack accessories – fasteners (1 set of 4) for additional security of racks | - | 8012-0531 |
| S 422 interface | modular plug distributor for 10 RS 422 interfaces | - | 8012-0295 |
| S 422 interface, cable 15 m) | RS 422 connection cable (15 m) between plug distributor and RS 422 interface | - | 5023-0036 |
| RS 422 interface, cable 50 m) | RS 422 extension cable (50 m) between interface converter and unit or RS 232 / RS 422 plug distributor | - | 5023-0117 |
| helf, perforated | Stainless steel | _ | 6004-0052 |

* Notes > See last page

Data Sheet Model KB 23

BINDER

| Designation | Description | * | ArtNo. |
|-----------------------------|--|----|-----------|
| Software | APT-COM™ communications software | | |
| | version 2 to 3, GLP edition | 19 | 9053-0016 |
| | version 3, BASIC edition | 19 | 9053-0014 |
| | version 3, GLP edition | 19 | 9053-0015 |
| | version 3, STANDARD edition | 19 | 9053-0013 |
| | APT-COM™ communications software, price: for free | | |
| | version 3, GLP DEMO Edition | 19 | 9053-0008 |
| Zero voltage relay contacts | for controlling 3 relay contacts via program regulators, accessible via 6-pin DIN socket (max. 24 V - 2.5 A) | | |
| | 230 V option model | - | 8012-0473 |

* Notes > See last page

SERVICES

| Designation | Description | * | ArtNo. |
|---|---|-------------------|-----------|
| Installation services | | | |
| Data Logger Kit installation service | unit function instructions for operation and programming of the controller | 18 | DL100500 |
| Installation | and set up of unit at operating location, connect to existing connections | 13, 18 | DL100100 |
| Preventive maintenance | | | |
| Preventive maintenance | Executive of equipment inspection according to maintenance plan | 14, 18 | DL200300 |
| Calibration services | | | |
| Calibration temperature | including certificate, one measuring point in center of chamber at specified temperature | 14, 16, 17, 18 | DL300101 |
| Temperature measurement 18 measuring points | including certificate, 18 measuring points at specified temperature | 14, 16, 17, 18 | DL300118 |
| Temperature measurement 27 measuring points | including certificate, 27 measuring points at specified temperature | 14, 16, 17, 18 | DL300127 |
| Temperature measurement 9 measuring points | including certificate, 9 measuring points at specified temperature | 14, 16, 17, 18 | DL300109 |
| Validation services | | | |
| Execution of IQ/OQ | in accordance with qualification folder | 15, 18, 20 | DL410200 |
| Execution of IQ/OQ/PQ | in accordance with customer's requirement, price: on request | 15, 18 | DL440500 |
| Qualification folder IQ/OQ | supporting documents for validation performed by customer, consisting of: IQ/OQ checklists, unit schematics, QM certificate in accordance with ISO 9001 | 15, 18, 20 | 8012-0873 |
| Qualification folder IQ/OQ/PQ | supporting documents for validation performed by customer, in accordance with customer's requirement, extension of Qualification folder IQ/OQ by chapter PQ | 15, 18 | 8012-0960 |
| Warranty service | | | |
| Extension of the warranty from 2 to 3 years | beginning with the date of delivery, wearing parts are not included | - | DL018041 |
| Extension of the warranty from 2 to 5 years | beginning with the date of delivery, wearing parts are not included | - | DL018042 |
| * Notoo - Soo loot nogo | | | |

* Notes > See last page



NOTES

- Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge. UL mark is not granted when this option is used. Heat resistant only to max. 200 °C. 01 02
- 03
- Only available on units rated for 230 V. 04
- 06 Heating-up time may increase as a result of the lower heat conductivity.
- 07 The additional heat input may affect the temperature behavior. Not in conjunction with the optional access port, door with window and interior lighting. 09
- 10 11 12 Not available on 23-liter units.
- Not available on 23- or 53-liter units.
- Only available on units rated for 230 V or 400 V.
- 13 Installation and connections take place at unit location; transport within the company only upon consultation.
- 14 We recommend a BINDER service contract to cover unit inspections, calibrations and validations.
- 15 OQ according to Yellow Paper = completed factory validation documentation of all OQ checklists.
- Sensor calibration is performed in an accredited calibration laboratory. 16
- 17
- Calibration is performed according to the BINDER factory standard. Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not 18 include a country-specific added fee (available on request).
- For additional accessories, refer to the Process documentation chapter. 19
- 20 When ordering IQ/OQ qualification folders and associated IQ/OQ execution on one order, we offer a 15 % discount for both items.
- When ordering IQ/OQ/PQ qualification folders and associated IQ/OQ/PQ execution on one order, we offer a 15 % discount for the item of the IQ/OQ/PQ folder.