# CC-108A

Clear View Circulator Bath consisting of transparent baths made of polycarbonate with temperature range up to max. 100°C. Powerful pressure and suction pump made of industrial plastic material. With adjustable overtemperature protection according to DIN 12876.

### Pilot ONF:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 11 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

3-2-2 warranty - registration required.

## Technical data according to DIN 12876

Operating temperature range with water cooling 20...100 °C with refrigerator Temperature stability at 70°C 0.02 K temperature set point / display Absolute accuracy Internal temperature sensor Pt100 Sensor external connection Pt100 Interface digital

Safety classification Heating power Pressure pump max. delivery max. delivery pressure Suction pump max. delivery (suction)

max. delivery pressure (suction) Pump connenction (optional)

Bath volume Filling capacity

Width bath opening WxD/ bath depth Overall dimensions WxDxH \*\*

Net weight

Power supply requirement

max. current

alternative power supply

alternative max. current min. Fuse (1 phase) max. Fuse (1 phase) Degree of Protection min. ambient temperature max. ambient temperature 25...100 °C

15...100 °C

5,7" colour Touchscreen setup for calibration

Ethernet, USB (Host u. Device), RS232 Class III / FL

2 kW

27 I/min 0.7 bar yes 25 I/min 0.4 bar M16x1 male

RΙ 6,6 I

130x210/ 150 mm 147x407x330 mm

6 kg

230V 1~ 50/60Hz

10 A

240V 1~ 60Hz

10 A 10A 16A IP20 5°C 40 °C



Order-No.: 2001.0002.01

from Serial-No.: 168886 1.0/13

# Technical data according to DIN 12876

Accessories and periphery: mini-USB cable #54949\*, Bath cover , Bath Bridges #19592, Cooling coil #30554, pump adaptor #19606, Note: When using Huber pump adapter: Polyglycol is not permissible to be used as a heat transfer fluid,polycarbonate test tube racks Typ A-F, nozzle #33288, DS level regulator #9580 \* standard equipment

Output data valid for: Room temperature  $20^{\circ}$  C In accordance with EN60034-1 the following voltage and frequency tolerances are valid: Voltage + / - 10%, as long as the frequency tolerance does not run in the opposite direction. Example: -10% voltage and +3% frequency -> not allowed!

Information to Electromagnetic compatibility: Classification (disturbance) to EN55011: Class B, Group 1

-10% voltage and -3% frequency -> allowed.

\*\* Please respect space requirements. See operating conditions at www.huber-online.com

Peter Huber Kältemaschinenbau GmbH Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com