



### C-MAG HS 10 IKAMAG®

New magnetic stirrer with heating and ceramic heating plate which offers excellent chemical resistance.

- Powerful motor for stirring quantities of up to 15 l (H<sub>2</sub>O)
- Fixed safety circuit of 550 °C
- Hot Top indicator >> hot surface warning to prevent burns!
- Exact temperature setting via digital display (LED)
- Bushing according to DIN 12878 for connecting a contact thermometer, e.g. ETS-D5, enables precise temperature control
- Digital error code display
- Elevated control panel for protection against leaking liquids

Accessories: ETS-D5, IKAFLON® 10 Magnetic stirring bar, IKAFLON® 15 Magnetic stirring bar, IKAFLON® 20 Magnetic stirring bar, IKAFLON® 25 Magnetic stirring bar, IKAFLON® 30 Magnetic stirring bar, IKAFLON® 40 Magnetic stirring bar, IKAFLON® 50 Magnetic stirring bar, IKAFLON® 80 Magnetic stirring bar, TRIKA® 25 Magnetic stirring bar, TRIKA® 40 Magnetic stirring bar, RS 1 Set of magnetic stirring bars, RSE Stirring bar remover, H 16 V Support rod

#### Technical Data

Number of stirring positions	1
Stirring quantity max. per stirring position (H <sub>2</sub> O) [l]	15
Stirring quantity max. (H <sub>2</sub> O) [l]	15
Motor rating input [W]	15
Motor rating output [W]	1.5
Speed display	scale
Speed range [1/min]	100 - 1500
Stirring bar length max. [mm]	80
Heat output [W]	1500
Heating rate (1 l H <sub>2</sub> O in H15) [K/min]	5
Heating temperature range [°C]	50 - 500
Heat control	LED
Heat control accuracy [±K]	10
Speed control	scale 0 - 6
Fixed safety circuit [°C]	550
Connection for ext. temperature sensor	ETS-D 4 fuzzy
Control accuracy with sensor [±K]	3
Temperature constancy in medium [±K]	3
Set-up plate material	ceramic
Set-up plate dimensions [mm]	280 x 280
Dimensions (W x H x D) [mm]	300 x 105 x 415
Weight [kg]	6
Permissible ambient temperature [°C]	5 - 40
Permissible relative moisture [%]	80
Protection class according to DIN EN 60529	IP 21
Voltage [V]	230
Frequency [Hz]	50/60
Power input [W]	1520
<b>Ident. No.</b>	<b>3581400</b>