
Moisture analyser KERN DLB









Robust moisture analyser for samples up to 160 g















3 YEARS
GUARANTY

KERN	DLB 160-3A		
Readout [d]	0,001 g / 0,01 %		
Weighing range [Max]	160 g		
Reproducibility, weight of sample 10 g	0,05 %		
Display after drying (Display can be switched over at any time)			
Moisture [%] = Weight loss (WL) from SW (startweight)	0 - 100 %		
Dry mass [%] = Residual weight (RW) from SW	100 - 0 %		
ATRO [%] (SG : RG) · 100%	100 - 999 %		
Weight loss [g] (WL)	Absolute value in [g]		
Temperature range	35 °C - 160 °C in steps up to 1 °C		
Drying modes	• J Standard drying		
	• 🖵 Pre-heat level, can be switched on		
Switch off criteria	 When the set time has expired 1 min - 99 min When the weight loss per unit of time falls below the target value (60 sec) 		
Recall of measurement	 Continuous output (residual weight) At the end of the drying process, manual or automatic (only in connection with KERN YKB-01N printer or PC) 		
Overall dimensions WxDxH	210x340x225 mm		
Net weight	approx. 4,2 kg		

Features

- Backlit LCD display, digit height 17 mm
 Current moisture content in %
 Unit for displaying the results, e.g. % moisture
- 3 Drying process active
- 4 Halogen quartz glass heater 400 W
- **Internal memory** for automatic sequence of 5 complete drying processes
- The last value measured remains on the display until it is replaced by a new measurement
- 10 sample plates included
- Table of applications: There are many practical examples in the operating instructions

Options

- Sample plates aluminium, Ø 92 mm. Unit of 80 pieces, KERN MLB-A01
- Round fiberglass filter e.g. for samples that splash or become encrusted. Unit of 80 pieces, KERN RH-A02
- 5 Temperature calibration set consists of measuring sensor and display device, KERN DLB-A01
- Protective working cover standard, can be reordered, KERN PLJ-A01
- Thermal printer, KERN YKB-01N

KERN Pictograms



Internal adjusting (CAL): Quick setting of the balance's accuracy with internal adjusting weight (motordriven).



Rechargeable battery pack: rechargeable set.



Battery operation: The battery type is specified for each device.



Data interface: The type of interface is shown by the pictogram. See the glossary for further details.



Dynamic weighing: Strong vibrations are filtered out to determine a stable weighing result.



Net-total weighing: weight of tare cup and weight of components memorized in two separate stores.



Percentage determination: Determining the deviation in % from the target value (100%).



Package shipment via courier.



Adjusting program (CAL): For quick setting of the balance's accuracy. External adjusting weight required.



Power supply: integrated in balance. 230V/50Hz in Germany. On request GB, AUS or USA version.



Piece counting: Reference quantities selectable. Display can be switched from piece to weight



GLP/ISO record keeping of weighing data with date, time and identification-no. Only with printers from KERN.



Stainless steel: the balance is protected against corrosion.



Suspended weighing: load support with hook on the underside of the balance.



Weighing with tolerance range: Upper and lower limiting can be programmed individually, e.g. dosing/sorting.



Pallet shipment via freight forwarder.



Weighing units: Can be switched to e.g. nonmetric units at the touch of a key. See balance model. Please refer to KERN's website for more details.



Mains adapter: 230V/50Hz in standard version for Germany. On request GB, AUS or USA version.



Spray and dust protection IPxxThe type of protection is shown by the pictogram. For details see the glossary.



Tare: put back displayed value to "0" during weighing process, e.g. to add or remove weighing material from a container.



Warranty: The warranty period is shown in the pictogram.



Verification possible: The time required for verification is specified in the pictogram.



DKD calibration possible: The time required for DKD calibration is specified in the pictogram.



For details on weighing technologies, see the glossary.

Precision is our business

To ensure the high level of precision of your balance, KERN offers the appropriate test weight package for your balance. This consists of the test weight, box and DKD calibration certificate, as proof of its accuracy. The best way to ensure proper balance calibration.

In the extensive KERN test weight range, you will find test weights in the international OIML error limit classes: E1, E2, F1, F2, M1, M2, and M3 with weights from 1 mg to 2000 kg.

The KERN DKD calibration laboratory for electronic balances and weights has been accredited by DKD since 1994 and today is one of the most modern and best-equipped DKD calibration laboratories for balances, test weights and force-measurement in Europe.

(DKD = German Calibration Service)

Thanks to the high level of automation, we can carry out DKD calibration of balances, test weights and force-measuring devices 24 hours a day, 7 days a week.

Range of services:

- DKD calibration of balances with a maximum load of up to 6000 kg
- DKD calibration of weights in the range of 1 mg 500 kg
- Database supported management of checking equipment and reminder service
- Calibration of force-measuring devices
- DKD calibration certificates in the following languages
 D, GB, F, I, E, NL, PL

Do you have questions about your scale, the corresponsing test weight or the calibration service? Your KERN specialist dealer will be pleased to assist you.

Your KERN specialist dealer:

KERN - Professional measuring. Measuring technology and testing services from a single source









